

## Floor Boxes

### Flush Rectangular Concrete Floorboxes

### 3-Gang/ Multiservice

#### Features

- For Use In Slab on Grade, 2nd Floor and Above Concrete Floors
- Cast Iron Base and Stamped Steel Top with Green Corrosion-Resistant Paint
- (8) 1" Threaded Hubs, Ships with (4) 1" to 3/4" Threaded Reducers
- 3.50" minimum depth of pour
- 1.25" prepour and 0.875" post pour adjustment

#### Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Rectangular	On/ Above Grade	783585696089	FB4333

#### Listings

cULus Listed  
UL 514A Listed  
CSA C22.2 No 18 certificated

#### Specifications

Box Base Material	Cast Iron
Box Top Material	Stamped Steel
Box Finish	Green Powder Paint
Concrete Cover	Tin Plate
Cover Frame Material	Thermoplastic
Device Chamber Grounding	(3) 6" Long #12 AWG Solid Copper Wire
Low Voltage Divider	(2) Stamped Steel
Wiring Chamber Volumes	(2) 36.5 IN <sup>3</sup> [598.2 CM <sup>3</sup> ]; 34.8 IN <sup>3</sup> [570.3 CM <sup>3</sup> ] center gang

#### Performance

##### Mechanical

1" to 3/4" Threaded Reducer	4 Each
Box Height	3.40" [86.4mm]
Box Length	4.91" [124.7mm]
Box Width	11.41" [289.8mm]
Concrete Pour- Minimum Depth	3.50" [95.3mm]
Concrete Pour- Post Pour Adjustment	.875" [22.2mm]
Threaded Hubs	(8) 1" NPT

# HUBBELL



#### Related Products

Brass Cover Flange	S5017GR
Aluminum Cover Flange	SA5017GR
Brass Surface Flange	SB3085W
Aluminum Surface Flange	SA3085W

#### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

