

Kellems® Wire Management Products
PolyTuff® I Non-Metallic Liquidtight Conduit
Liquidtight Conduit

HUBBELL

Features

- No jagged metal edges
- Rigid PVC core bonded to flexible PVC jacket
- Non-metallic construction ends metal fatigue and separation problems

Ordering Information

Description	Device Color	UPC Number	Catalog Number
Non-Metallic, PolyTuff® I Conduit, Gray	Gray	78358558662	G1038R1200



Online Resources

eCatalog

Listings

UL Listed
CSA Certified

Specifications

Material	Co-extruded rigid and flexible PVC
Trade Size	3/8 Inch
Bend Radius Inches (mm)	2.00" (50.8)
Conduit ID/OD Inches (mm)	.49"/.70" (12.6/17.8)

Performance

Electrical	
Voltage Rating	600V Maximum
Environmental	
Operating Temperature	Wet Env. 0°F to +140°F (-18°C to +60°C) Oil Env. 0°F to +158°F (-18°C to +70°C) Dry Env. 0°F to +140°F (-18°C to +60°C)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

