

Kellems® Wire Management Products  
PolyTuff® I Non-Metallic Liquidtight Conduit  
Liquidtight Conduit

# HUBBELL

## Features

- No jagged metal edges
- Rigid PVC core bonded to flexible PVC jacket
- Non-metallic construction ends metal fatigue and separation problems

## Ordering Information

Description	Device Color	UPC	Catalog Number
Non-Metallic, PolyTuff® I Conduit, Gray	Gray	783585498003	G1075



## Listings

UL Listed  
CSA Certified

## Online Resources

[eCatalog](#)

## Specifications

Material	Co-extruded rigid and flexible PVC
Trade Size	3/4 Inch
Bend Radius Inches (mm)	4.00" (101.6)
Conduit ID/OD Inches (mm)	.83"/1.04" (21.1/26.4)

## Performance

### Electrical

Voltage Rating 600V Maximum

### Environmental

Operating Temperature Wet Env. 0°F to +140°F (-18°C to +60°C)  
Operating Temperature Oil Env. 0°F to +158°F (-18°C to +70°C)  
Operating Temperature Dry Env. 0°F to +140°F (-18°C to +60°C)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

