

Ground Fault Products

Portable GFCI

Hardwired 60A GFCI

HUBBELL

Features

- High impact UV stabilized housing for long life
- Class A GFCI protection
- Type 4X environmental rating
- 1" Conduit hubs
- Flying leads for electrical circuit splicing

Ordering Information

Description	UPC	Catalog Number
Hardwired GFCI, 60A, 3-Phase 208V AC, UL Type 4X, 4-6mA Trip Level, Automatic Set	783585708768	GFHW86108

Listings

UL 943
cULus

Specifications

Voltage	3Ø 208V AC
Operating Voltage Range	85% to 110% of rating
Current	Up to 60 Amps
Frequency	60 Hz
Trip Level	5mA +/- 1mA
Response Time	25ms max at 500 O Fault
Reset Type	Automatic
Operating Temperature	-35° C to 50° C (-31° F to 122° F)
Enclosure Rating	NEMA 4X
Latching Mechanism	AC Contactor



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

