

Ground Fault Products

Portable GFCI

Cord Drop

HUBBELL

Features

- High impact UV stabilized housing for long life
- TYPE 4x and 6P wet location rated for indoor/outdoor applications
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral
- Self-test functionality in accordance with UL 943

Ordering Information

Description	Cord Length	UPC	Catalog Number
Portable GFCI cord drop, 20A, 208V AC, 10' black SEOOW cable and Kellems mesh strain relief, automatic set	10'	783585708652	GFP202081P



Listings

UL 943
cURus

Specifications

Voltage	208V AC
Operating Voltage Range	85% to 110% of rating
Current	Up to 20 Amps
Frequency	60 Hz
Trip Level	5mA +/- 1mA
Response Time	25ms max at 500 O Fault
Reset Type	Automatic
Operating Temperature	-35°C to 66°C (-31° F to 150° F)
Enclosure Rating	NEMA 4X, 6P
Latching Mechanism	Electro-magnetic

Online Resources

[Customer Sales Drawings](#)
[eCatalog](#)
[Installation Instructions](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

