

Ground Fault Products

Portable GFCI

Field Wireable Inline

Features

- High impact UV stabilized housing for long life
- Watertight GFCI housing for use in harsh environments
- Open neutral protection Trips upon loss of neutral
- LED indicated power status
- Local set and reset buttons on device

Ordering Information

Description	UPC	Catalog Number
Portable GFCI Field Wireable Inline, 20A 125V AC	783585694177	GFP20FWM

Listings

UL 943
cULus

Specifications

Voltage	120V AC
Operating Voltage Range	85% to 110% of rating
Current	Up to 20 Amps
Frequency	60 Hz
Trip Level	5mA +/- 1mA
Response Time	25ms max at 500 O Fault
Reset Type	Manual
Operating Temperature	-35°C to 66°C (-31° F to 150° F)
Enclosure Rating	Type 3R
Latching Mechanism	Electro-magnetic

HUBBELL



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

