

Ground Fault Products

Portable GFCI

Line Cord Twist-Lock®

HUBBELL

Features

- High impact UV stabilized housing for long life
- IP69K GFCI housing for use in harsh environments
- Self-test functionality in accordance with UL 970

Ordering Information

Description	Cord Length	UPC	Catalog Number
GFCI Line Cord, Twist-Lock®, Manual Set, 20A, 120V AC, L5-20, 2', 12/3 SJTW	2'	783585694450	GFPIST20125L KM

Listings

UL 943
cULus

Specifications

Voltage	120V AC
Operating Voltage Range	85% to 110% of rating
Current	Up to 20 Amps
Frequency	60 Hz
Trip Level	5mA +/- 1mA
Response Time	25ms max at 500 O Fault
Reset Type	Manual
Operating Temperature	-35°C to 66°C (-31° F to 150° F)
Enclosure Rating	TYPE 4X, IP69, & IP69K
Latching Mechanism	Electro-magnetic



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

