

Ground Fault Products

Portable GFCI

Line Cord Twist-Lock®

HUBBELL

Features

- High impact UV stabilized housing for long life
- IP69K GFCI housing for use in harsh environments
- Self-test functionality in accordance with UL 971

Ordering Information

| Description | Cord Length | UPC | Catalog Number |
|---|-------------|--------------|--------------------|
| Line Cord, Twist-Lock®, Automatic Set, 20A, 250V AC, L6-20, 2', 12/3 SJTW | 2' | 783585694467 | GFPIST20250L KM |

Listings

UL 943
cULus

Specifications

| | |
|-------------------------|----------------------------------|
| Voltage | 250V AC |
| Operating Voltage Range | 85% to 110% of rating |
| Current | Up to 20 Amps |
| Frequency | 60 Hz |
| Trip Level | 5mA +/- 1mA |
| Response Time | 25ms max at 500 O Fault |
| Reset Type | Manual |
| Operating Temperature | -35°C to 66°C (-31° F to 150° F) |
| Enclosure Rating | TYPE 4X, IP69, & IP69K |
| Latching Mechanism | Electro-magnetic |



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

