

Ground Fault Products

Portable GFCI

30A Line Cord

HUBBELL

Features

- High impact UV stabilized housing for long life
- TYPE 4x and 6P wet location rated for indoor/outdoor applications
- Red blinking light plus optional audible alarm
- Open neutral protection Trips upon loss of neutral
- Self-test functionality in accordance with UL 943

Ordering Information

Description	Cord Length	UPC	Catalog Number
Portable GFCI, 30A, 120V AC, 6' Cord Length, 10/3 SJGOOW, UL Type 4X, 4-6mA Trip Level, Automatic Set, Yellow	6'	783585703145	GFPST1315



Listings

UL 943
cURus

Specifications

Voltage	120V AC
Operating Voltage Range	85% to 110% of rating
Current	Up to 30 Amps
Frequency	60 Hz
Trip Level	5mA +/- 1mA
Response Time	25ms max at 500 O Fault
Reset Type	Automatic
Operating Temperature	-35°C to 66°C (-31° F to 150° F)
Enclosure Rating	NEMA 4X, 6P
Latching Mechanism	Electro-magnetic

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

