

Ground Fault Products

Commercial Standard GFCI Receptacles

Features

- Patented AUTOGUARD® self test technology
- Internal back wiring clamp and guide for quick and secure termination
- Triple wipe construction
- Alarm version provides audible notification of a trip condition

Ordering Information

Description	Catalog Number	UPC	Color
15A, 125V, Style Line®, AUTOGUARD® self test GFCI receptacle, alarm, flush face, back and side wired,	GFRST15RB	883778228063	GFRST15RB

Listings

UL Listed - Canadian and U.S.  
Meets ADA Standards  
Meets all NEC® requirements  
CSA Certified  
NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Zinc plated steel
Mounting Screws	Zinc plated steel

Performance

<b>Electrical</b>	
Amperage	15A/20A, 20A Feed Thru
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum
Frequency	60 Hz
Maximum Interrupting Capacity	10,000A
Trip Level	4 to 6 mA
Trip Time	.025 second nominal
Voltage	120V AC +10% - 15% (102V to 132V)
<b>Mechanical</b>	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA
<b>Environmental</b>	
Flammability	UL 94V-2
Operating Temperature	-35°C to 66°C or -30°F to 150°F

HUBBELL



Accessories

Wallplates for duplex openings

Online Resources

eCatalog