

## Ground Fault Products

# Commercial Standard Hospital Grade GFCI Receptacles

# HUBBELL

### Features

- Green power indicator and red trip indicator
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Alarm version provides audible notification of a trip condition

### Ordering Information

Description	Color	UPC	Catalog Number
20A, 125V, Style Line®, hospital grade, AUTOGUARD® self test GFCI receptacle, alarm, flush	Brown	783585534121	GFRST83B

### Listings

UL Listed - Canadian and U.S.  
Meets ADA Standards  
Meets all NEC® requirements  
CSA Certified  
NEMA® WD-6 Compliant

### Specifications


Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Brass
Mounting Screws	Zinc plated steel

### Performance

Electrical	
Amperage	15A/20A, 20A Feed Thru
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum
Frequency	60 Hz
Maximum Interrupting Capacity	10,000A
Trip Level	4 to 6 mA
Trip Time	.025 second nominal
Voltage	120V AC +10% - 15% (102V to 132V)

Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

Environmental	
Flammability	UL 94V-2
Operating Temperature	-35°C to 66°C or -30°F to 150°F



### Accessories

Wallplates for duplex openings

### Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

