Ground Fault Products Heavy Duty Commercial Tamper-Resistant GFCI Receptacles

HUBBELL

Features

- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction
- Single LED status indicator green indicates power, red indicates a trip, flashing red indicates end of life

Ordering Information

Description 15A, 125V, Style Line®, AUTOGUARD® self test GFCI receptacle, tamper-resistant, flush face, back and side wired, tri-drive screws

Color White UPC 883778999628 Catalog Number GFRTR15W

Listings

UL Listed - Canadian and U.S.
UL 943 Class A for GFCIs UL File E41978
Meets ADA Standards
Meets all NEC® and CEC requirements
CSA Certified
NEMA® WD-6 ANSI 73 Compliant

Specifications

Face Nylon
Base Nylon
Power Contacts Brass
Ground Contacts Brass

Mounting StrapZinc plated steelMounting ScrewsZinc plated steelAuto-Ground StapleStainless steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage

Trip Level Withstands 1,500V minimum

rip Level 4 to 6 mA

Trip Time .025 second nominal

Frequency 60 Hz

Voltage 120V AC +10% - 15% (102V to 132V)

Amperage 15A/20A, 20A Feed Thru

Maximum Interrupting Capacity 10,000A

Mechanical

Product Identification Ratings are a permanent part of the device Terminal Accommodation #14-#10 AWG copper stranded or solid

conductor only

Terminal Identification Terminals identified in accordance with UL

498 and CSA

Environmental

Flammability UL 94V-2

Operating Temperature -35°C to 66°C or -30°F to 150°F

Accessories

Wallplates for duplex openings

Online Resources

Customer Use Drawing eCatalog

Installation Instructions

