

Ground Fault Products  
 Heavy Duty Commercial Weather Resistant  
 GFCI Receptacles

# HUBBELL

## Features

- Patented AUTOGUARD® self test technology
- Meets NEC requirements for weather resistance (406.9), UV and corrosion resistance for harsh and damp applications
- Protects against line and load reversal, no power to the face or downstream if device is miswired
- Single LED status indicator - green indicates power, red indicates a trip, flashing red indicates end of life

## Ordering Information

Description	Color	UPC	Catalog Number
15A, 125V, Style Line®, AUTOGUARD® self test GFCI receptacle, weather resistant, flush face, back and side wired, tri-drive screws	Brown	883778999710	GFRWR15

## Listings

UL Listed - Canadian and U.S.  
 UL 943 Class A for GFCIs UL File E41978  
 Meets ADA Standards  
 Meets all NEC® and CEC requirements  
 CSA Certified  
 NEMA® WD-6 ANSI 73 Compliant

## Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Zinc plated steel
Mounting Screws	Zinc plated steel
Auto-Ground Staple	Stainless steel

## Performance

### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 1,500V minimum
Trip Level	4 to 6 mA
Trip Time	.025 second nominal
Frequency	60 Hz
Voltage	120V AC +10% - 15% (102V to 132V)
Amperage	15A/20A, 20A Feed Thru
Maximum Interrupting Capacity	10,000A

### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14-#10 AWG copper stranded or solid conductor only
Terminal Identification	Terminals identified in accordance with UL 498 and CSA

### Environmental

Flammability	UL 94V-2
Operating Temperature	-35°C to 66°C or -30°F to 150°F

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



## Accessories

Wallplates for duplex openings	
Solid Right Angle Pigtailed Terminal	SNAP1RA
Stranded Right Angle Pigtailed Terminal	SNAP2RA

## Online Resources

Customer Use Drawing  
 eCatalog  
 Installation Instructions

