

## Industrial Grade Extra Heavy Duty Ground Fault Receptacle

### Autoguard Self-Test GFCI

## 20A, Hospital Grade, Tamper-Resistant, Weather-Resistant

# HUBBELL

### Features

- Heavy duty robust construction, high impact resistant polyester housing
- Corrosion Resistant: nickel-plated face contacts, mounting strap, line/load terminals and terminal clamps, stainless steel screws
- Patented auto monitor, power denial technology

### Ordering Information

Description	Color	UPC	Catalog Number
20A, 125V, Style Line, AUTOGUARD self test GFCI receptacle, hospital grade, tamper-resistant and weather-resistant, flush face, back and side wired	Red	783585746098	GFSG8300R



### Related Products

Accessories

(1) Matching Nylon and (1) Stainless Steel Wall Plate Included

### Listings

UL Listed - Canadian and U.S.  
Meets ADA Standard  
Meets all NEC requirements  
CSA Certified  
Fed Spec  
NEMA WD-6 Compliant

### Specifications

Face	PC/PBT
Base	Nylon
Power Contacts	Nickel Plated Brass
Ground Contacts	Nickel Plated Brass
Mounting Strap	Nickel Plated Brass
Mounting Screw	Stainless Steel

### Performance

#### Construction

Grounding	Autoground Clip
Terminal	#14 to #10AWG
Termination	Back and Side

#### Electrical

Dielectric	Withstand 1,500V
Feed-through	20 Amp Protection
Flammability	V0 per UL 94
Frequency	60 Hz
Operating Temp	-35 C to 66 C
Short Circuit	10,000 Amps
Trip Level	4 mA to 6mA (0.025 sec)
Voltage	120V AC (-15%, +10%)

#### Electrical Ratings

Amperage	20A
----------	-----

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

