

Replaced by GFRTR20C2I

Ground Fault Products  
Marked Controlled Commercial Tamper-Resistant GFCI  
Receptacles

Marked Controlled Commercial Tamper-Resistant GFCI Receptacles



Features

- Permanently marked "controlled" ground fault receptacle
- Patented shutter design for tamper-resistant
- Compliant with NEC® 406.12 and NEC® 517-18(c)
- Patented AUTOGUARD® self test technology
- Triple wipe construction

Online Resources

eCatalog

Ordering Information

Description	Color	UPC Number	Catalog Number
20A, 125V, Style Line®, AUTOGUARD® self test GFCI receptacle, marked controlled, tamper-resistant, flush face, back and side wired, multiple drive screws	Ivory	783585596792	GFTRST20IMC

Listings

UL Listed - Canadian and U.S.  
Meets all NEC® requirements  
CSA Certified  
NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Zinc plated steel
Mounting Screws	Zinc plated steel

