Ground Fault Products Commercial Tamper-Resistant and Weather Resistant GFCI Receptacles



Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

Ordering Information

V			
Description	Color	UPC	Catalog Number
20A, 125V, Style	lvory	883778124389	GFTWRST20IU
Line®, assembled in			
the USA,			
AUTOGUARD® self			
test GFCI receptacle,			
tamper-resistant and			
weather resistant, flush			
face, back and side			
wired, multiple drive			
screws			


Listings

UL Listed - Canadian and U.S. Meets ADA Standards Meets all NEC® requirements CSA Certified NEMA® WD-6 Compliant

Specifications

Face	Nylon
Base	Nylon
Power Contacts	Brass
Ground Contacts	Brass
Mounting Strap	Zinc plated steel
Mounting Screws	Zinc plated steel





Online Resources

Customer Use Drawing eCatalog Installation Instructions

