Ground Fault Products Commercial Tamper-Resistant and Weather **Resistant GFCI Receptacles**



Features

- Patented shutter design for tamper-resistant protection
- Meets NEC requirements for TR (517-18c) and WR (406.9), UV and corrosion resistance for harsh and damp applications
- Patented AUTOGUARD® self test technology
- Protects against line and load reversal, no power to the face or downstream if device is miswired

UPC

Ordering Information


Description	Color
20A, 125V, Style	White
Line®, hospital grade,	
AUTOGUARD® self	
test GFCI receptacle,	
tamper-resistant and	
weather resistant, flush	
face, back and side	
wired, multiple drive	
screws	

UL Listed - Canadian and U.S. Meets ADA Standards Meets all NEC® requirements

NEMA® WD-6 Compliant

Catalog Number 783585485416 GFTWRST83W





Online Resources

Customer Use Drawing eCatalog Installation Instructions

Specifications

Listings

CSA Certified

Ground Contacts	Brass
Mounting Strap	Brass
Mounting Screws	Zinc plated steel
Face	Nylon
Base	Nylon
Power Contacts	Brass



Dimensions in Inches (mm) Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.