

Kellems® Wire Management Products
Strain Relief for Liquidtight Conduit
Liquidtight Conduit Grips

HUBBELL

Features

- Helps prevent conduit pull-out and damage at fitting
- Reduces equipment downtime

Ordering Information

Description	Style	UPC	Catalog Number
Liquidtight Conduit, 90° Male Hubbell Fitting	90 Degree	783585334868	H0509CNK

Listings

UL Listed
CSA Certified

Specifications

Strand	Stainless Steel
Strand Length	4.5" (11.43)
NPT Fitting Size	1/2 Inch
Conduit Trade Size	1/2 Inch

Performance

Environmental

Flammability	UL 94-HB and UL 94-V2
Hazardous Location	Suitable for use in hazardous locations per Class I, Div. 2, Class II, Div. 1 & 2, Class III, Div. 1 & 2
Operating Temperature	-30°F to +225°F (-34°C to +107°C)



Online Resources

[eCatalog](#)
[Installation Instructions](#)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

