

## Switches, Three Way

15A, 120-277V AC

# EdgeConnect™ Extra Heavy Duty Industrial Switch

# HUBBELL

### Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Strip gauge for accurate wiring
- Automatic self-grounding clip

### Ordering Information

| Description   | Color | UPC         | Catalog Number |
|---------------|-------|-------------|----------------|
| 3-Way, Toggle | Gray  | 78358596355 | HBL1203STGY    |

### Listings

UL Listed  
CSA Certified  
Fed Spec

### Specifications

|                 |               |
|-----------------|---------------|
| Material        | Polycarbonate |
| Contacts        | Silver Alloy  |
| Mounting Bridge | Brass         |

### Performance

|                         |  |
|-------------------------|--|
| <b>Electrical</b>       |  |
| Dielectric Voltage      | Withstands 1500V AC minimum for 1 minute       |
| Max. Continuous Current | 15A  |
| Max. Working Voltage    | 277V AC  |
| Overload                | Minimum 4.8 times rated current for 100 cycles |
| Temperature Rise        | 30°C maximum at rated current                  |

### Mechanical

|                         |   |
|-------------------------|---|
| Terminal Accommodations | #14 AWG min. - #10 AWG max. solid and stranded copper wire only |
|-------------------------|---|

### Environmental

|                       |  |
|-----------------------|--|
| Flammability          | UL 94V-2   |
| Operating Temperature | Max. continuous: 75°C; Min. continuous: -40°C without impact |



### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

