

Switches, Three Way  
20A, 120-277V AC  
EdgeConnect™ Extra Heavy Duty Industrial  
Illuminated Switch

HUBBELL

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Strip gauge for accurate wiring
- Automatic self-grounding clip

Ordering Information

Description	Color	UPC	Catalog Number
3-Way, Toggle	White	78358596404	HBL1223STILW

Listings

UL Listed  
CSA Certified  
Fed Spec

Specifications

Material	Polycarbonate
Contacts	Silver Alloy
Mounting Bridge	Brass

Performance

<b>Electrical</b>	
Dielectric Voltage	Withstands 1500V AC minimum for 1 minute
Max. Continuous Current	20A
Max. Working Voltage	277V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current

<b>Mechanical</b>	
Terminal Accommodations	#14 AWG min. - #10 AWG max. solid and stranded copper wire only

<b>Environmental</b>	
Flammability	UL 94V-2
Operating Temperature	Max. continuous: 75°C; Min. continuous: -40°C without impact



Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

