Watertight Devices 20A, 125V, 2 Pole, 3 Wire Straight Blade Plug

HUBBELL

Features

- Power indicating LED also confirms wiring condition of the device
- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection

Ordering Information

Description Thermoplastic elastomer clear plug

Cord Diameter UPC Number 0.375"-0.625" 78358558059

Catalog Number HBL14W33AWC

(9.5-15.9)

Listings

Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA WD-1, WD-6 and ANSI standards UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P

Specifications

Body Thermoplastic Elastomer Blade Holder White Nylon

Clear polycarbonate Terminal Retainer Nickel plated brass Blades White Nylon Core **Bushing & Cone Seal Black Elastomer**

Gotcha Ring Nylon Strain Relief Nut PBT

Nickel plated brass **Terminal Screws**

Performance

Electrical

Current Interrupting Rated for current interruption per UL498

Dielectric Voltage 2500V AC Max Working Voltage As marked

Temperature Rise 30°C max per UL498 at rated current

Mechanical

Cord Accomodation 0.375"-0.625" (9.5-15.9)

Environmental

UL Listed 4, 4X, 12, 6, 6P Moisture Resistance

Operating Temperature -40°C (without impact) to +60°C continuous **UV** resistance All exposed materials are UV stabilized



Complementary Products

Watertight Connector HBL15W33AWC Watertight Receptacle with Lift Cover **HBL60W33**

Watertight Duplex Receptacle HBL60W33D

Online Resources

eCatalog Installation Instructions

