

Switches

15A, 120/277V AC

HBL[®] Extra Heavy Duty Industrial Series,
Momentary Contact, Specification Grade, Three
Position, Two Circuit, Center OFF

HUBBELL

Features

- Large brass binding head screws with deep slots
- Abuse resistant nylon toggle
- Strip gauge for accurate wiring

Ordering Information

Description	Toggle Color	UPC Number	Catalog Number
Nylon toggle, back and side wired.	Light Almond	783585189321	HBL1556LA

Listings

UL Listed

Specifications

Dimensions	4.06 in x 1.31 in x 1.89 in
------------	-----------------------------

Performance

Electrical	
Dielectric Voltage	Withstands 1500V AC minimum for 1 minute
Max. Continuous Current	15A
Max. Working Voltage	277V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current

Mechanical	
Terminal Accommodations	#14 AWG min. - #10 AWG max. Solid and stranded copper wire only

Environmental	
Flammability	UL 94V-2
Operating Temperature	Max. continuous: 75°C, Min. continuous: -40°C without impact



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

