

Switches

20A, 120/277V AC

HBL[®] Extra Heavy Duty Industrial Series,
Momentary Contact, Specification Grade, Three
Position, Two Circuit, Center OFF

HUBBELL

Ordering Information

Description	Toggle Color	UPC Number	Catalog Number
Nylon toggle, back and side wired.	Light Almond	783585189338	HBL1557LA

Listings

UL Listed

Specifications

Dimensions	4.06 in x 1.31 in x 1.89 in
------------	-----------------------------

Performance

Electrical	
Dielectric Voltage	Withstands 1500V AC minimum for 1 minute
Max. Continuous Current	20A
Max. Working Voltage	277V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current
Mechanical	
Terminal Accommodations	#14 AWG min. - #10 AWG max. Solid and stranded copper wire only
Environmental	
Flammability	UL 94V-2
Operating Temperature	Max. continuous: 75°C, Min. continuous: -40°C without impact



Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

