# Single Pole Devices and Temporary Power 150A, 600V AC/DC Female Plugs

### Features

- Extra Long non-conductive inner sleeve
- · Turn and Lock Symbol aids in the mating of devices
- · Easily Identifiable Cable with cut off points for secure fit

**Device Color** 

White

## **Ordering Information**

**Description** 150A, thermoplastic elastomer,cable size #8 - #2 AWG

#### Listings

UL and cUL Listed UL Enclosure Types 3R, 4X, 12 National Electric Code (NEC), ANSI/NFPA 70

## **Specifications**


Base Compound Contact Material Retaining Screw Material Thermoplastic Elastomer (TPE) Brass Nylon

**UPC Number** 

783585458380

**Catalog Number** 

HBL15FW



CROSS PIN

## Performance

**Electrical** Amperage Rating Voltage Rating

**Terminal Accommodation** 

Mechanical Product Identification 150A Maximum 600V AC/DC Maximum

Ratings are a permanent part of device #8 to #2 AWG



MALE PLUG BODY

Customer Sales Drawings eCatalog Installation Instructions



HUBBELL