

Temporary Power  
Temporary Industrial Lighting  
LED Stringer Lights



Features

- 90 LEDs for maximum illumination
- Very low heat output
- Magnetic base included for added hanging flexibility

Ordering Information

Description	UPC	Catalog Number
90 LEDs per fixture, light string with magnetic base included	783585528311	HBL182S20LED



Listings

UL
CSA
ETL

Online Resources

eCatalog
----------

Specifications

Light Type	LED
Plug Type	NEMA 5-15P
Included	Magnetic base

Performance

<b>Electrical</b>	
Lamp Life	50,000 hours
Lumen Output per Fixture	450
Rating	15A 125V
Watt per fixture	6.6
<b>Mechanical</b>	
Cord Length	20 ft.
Number of fixtures	1

