### Hubbellock® Devices 30A, 600V AC, 20A, 250V DC, 3 Pole, 4 Wire Grounding

# HUBBELL

## Hubbellock® Flanged Inlet

#### **Features**

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Metallic weather protective spring loaded cover provides protection from moisture and dust

#### **Ordering Information**

Description Black phenolic interior, aluminum housing	Device Color	UPC	Catalog Number
	Metallic	783585017457	HBL20418
alaminam nodoling			

#### Listings

Listed to UL Standard Certified to CSA Standard

#### **Specifications**

Housing	Cast Aluminum
Inlet Interior	Thermoset
Contacts	Brass
Terminal Screws	Zinc plated steel

#### **Performance**

**Electrical** 

**Current Interrupting** Certified for current interrupting at full rated current

Dielectric Voltage 2.000V minimum

Mechanical

Terminal Accommodation #10 AWG - #6 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498


**Environmental** 

UL 94 V0 for Receptacles and Inlets.HB or better for Plugs Flammability and Connectors

Moisture Resistance IP30 Suitability

**Operating Temperatures** Maximum Continuous 75°C; Minimum -40°C (w/o impact)





#### **Accessories**

Connector	HBL21414B
Corrosion Resistant Connector	HBL21CM414B

#### Resources

Customer Use Drawing eCatalog

