Hubbellock® Devices 30A,480V AC, 3 Pole, 4 Wire Grounding Hubbellock® Receptacle

HUBBELL

Features

- Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Thermoset molded housing provides maximum heat resistance

Ordering Information

Description Black phenolic, red	Device Color Red	UPC 783585017419	Catalog Number HBL20443
center insert	Reu	763363017419	HBL20443

Specifications

Device Color	Black/Red Shutter
Housing	Thermoset
Shutter	Thermoset
Contacts	Bronze
Bridge	Zinc plated steel
Terminal Screws	Zinc plated steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage 2,000V minimum

Mechanical

Terminal Accommodation #10 AWG - #6 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental


Flammability UL 94 V0 for Receptacles and Inlets.HB or better for Plugs

and Connectors

Moisture Resistance IP30 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)





Accessories

Plug	HBL20445B
Weatherproof Lift Cover	HBL7420WOR
Single Gang Stinless Steel	SS737
Wallnlate	

Resources

Customer Use Drawing eCatalog

