Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding

Heavy Duty Style Line® Decorator Receptacles

Features

- · Aesthetic Style Line® decorator design
- Triple wipe contacts

Ordering Information

Description	Device Color	UPC	Catalog Number
Back and side wired.	Brown	783585060422	HBL2162

Listings

UL Listed to UL498 File No. E2186 Certified to CSA 22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant

Specifications

Nylon **PBT** Base Contacts Brass Wire Clamp Plated brass **Terminal Screws** Brass

Mounting Strap .040 in. (1) Galvanized steel

Automatic Self-grounding Staple Stainless steel **Ground Contact** .031 in. (.8) Brass

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current Withstands 2,000V minimum Dielectric Voltage

Mechanical

Product Identification Ratings are a permanent part of the device **Terminal Accommodation** #12-#10 AWG copper stranded or solid conductor only

Terminal Identification Terminals identified in accordance with UL 498 and CSA

Environmental


Flammability Top: UL 94V-2, Base: UL 94V-0

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)

HUBBELL







Online Resources

Customer Use Drawing eCatalog Installation Instructions

Accessories

Wallplate or Weatherproof Cover StyleLine® De Opening

