

Panel Mount Switches
 10A 250V AC, 20A 125V AC
 Heavy Duty Panel Mount Switch

HUBBELL

Features

- Nickel Plated for Corrosion Resistance

Ordering Information

| Description | Terminal | UPC | Catalog Number |
|---|----------|--------------|----------------|
| Double pole/ double throw 3-position center off momentary | Spade | 783585017150 | HBL223SPMM |



Listings

UL Listed


Specifications

| | |
|----------------|-------------------------------------|
| Body Material | Impact Resistant Thermoplastic Body |
| Contacts | Fine Silver |
| Strap Material | Nickel Plated |
| Bushing | Brass- Nickel Plated |
| Toggle | Brass- Nickel Plated |

Performance

Environmental

Operating Temperatures Max Continuous- 75 °C, Minimum -40 °C Without Impact



Online Resources

Customer Use Drawing
 eCatalog