Hubbellock® Devices 20A, 125V, 2 Pole, 3 Wire Grounding Hubbellock® Plug

HUBBELL

Features

- Molded-in male contacts are resistant to damage and provide a consistently positive connection
- Insulated non-metallic housing enhances safety and abuse resistance
- Box terminals in conjunction with screws with pressure pads provide maximum termination strength and dependability
- Three-piece clamp assembly provides maximum strain relief and protects against entry of moisture and dust

Ordering Information

Description Cord Diameter UP- Nylon housing, 320"- 783 thermoset interior .660"(8.12-16.5)	PC Catalog Number 3585017440 HBL23035B
--	---



Listed to UL Standard Certified to CSA Standard

Specifications

Black/White
Nylon
Nylon
Thermoset
Brass
Stainless Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #12 AWG stranded copper wire only.


Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better Moisture Resistance IP30 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)





Accessories

Connector	HBL23032B
Single Receptacle	HBL23030

Resources

Customer Use Drawing eCatalog

