Twist-Lock Devices

20A, 250V AC, 2 Pole, 3 Wire Grounding

Screwless Terminated InsulGrip Flanged Receptacle

HUBBELL

Features

- · Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Backwired termination for ease of installation

Ordering Information

Description **UPC Catalog Number** Nylon casing, back wired 78358571931 HBL2326ST

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing Nylon Terminal Retainer Nylon Plunger Nylon Contacts **Brass Terminal Spring Clamp** Spring Steel Assemby Screws Zinc Plated Tri-drive

Weight (lbs) 0.35



Online Resources

Customer Sales Drawings eCatalog

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated

Dielectric Voltage Withstands 3,000V minimum

Mechanical

Terminal Accommodation #14 AWG - #10 AWG solid or #14 AWG - #8

AWG stranded copper wire

Terminal Identification Terminals identified in accordance with UL 498

Environmental

HB or better per UL94/CSA 22.2 No.0.17 Flammability

Moisture Resistance IP20 Suitability

Maximum Continuous 75°C, Minimum -40°C **Operating Temperatures**

(w/o impact)

