Twist-Lock® Devices 20A, 125/250V AC, 3 Pole, 3 Wire Non-Grounding Insulgrip® Flanged Inlet

HUBBELL

Features

- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Ordering Information

Description Catalog Number UPC Device Color Nylon casing, back White 783585128962 HBL2365 wired

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing Nylon

Terminal Retainer Clear polycarbonate

Blades **Brass**

#10-32 Brass (Phillips / Slotted / Robertson) **Terminal Screws**

Terminal Clamp Cold rolled steel - nickel plated

Assembly Screws Steel - nickel plated Nickel plated brass Mounting Screw

Performance

Dielectric Voltage

Electrical

Certified for current interrupting at full rated current **Current Interrupting**

Withstands 2,000V minimum

Mechanical

#16 AWG - #8 AWG solid or stranded copper wire only. Cord Grip Accomodation **Terminal Identification**

Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C.Minimum -40°C (w/o impact)



Accessories

Connector	HBL2363
Weatherproof Lift Cover	WP2

Resources

eCatalog

