### Twist-Lock® Devices 20A, 250V AC; 2 Pole, 3 Wire Grounding Corrosion Resistant Insulgrip® Connector

# HUBBELL

#### **Features**

- Ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Integral dust shield protects wiring chamber from dust or contaminants.

**Ordering Information** 

Catalog Number Description Cord Diameter Corrosion resistant, 783585038124 .360" - .930"(9-24) HBL23CM23 yellow nylon.



#### Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

#### **Specifications**

Nylon Terminal Retainer Clear polycarbonate Nickel Plated Brass

#10-32 Bronze (Phillips / Slotted / Robertson) **Terminal Screws** 

Cold rolled steel - nickel plated

Assembly Screws Steel - nickel plated

## Housing / Cord Clamp

Contacts

**Terminal Clamp** 

#### **Performance**

**Electrical** 

**Current Interrupting** Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

#16 AWG - #8 AWG stranded copper wire only. **Terminal Accommodation** 


Terminal Identification Terminals identified in accordance with UL 498

**Environmental** 

HB or better per UL94 or CSA 22.2 No. 0.6 Flammability

Moisture Resistance IP20 Suitability

**Operating Temperatures** Maximum Continuous 75°C Minimum -40°C (w/o impact)



#### **Accessories**

Ø 1.970 ±.015 [50.04 ±0.38]

Plug	HBL23CM21
Weatherproof Boot	HBL60CM32

#### Resources

Customer Use Drawing eCatalog

