

Twist-Lock[®] Edge Devices

20A 125/250V AC, 3- Pole 4-Wire

Screwless Terminated InsulGrip[®] Plug



- Features
- Faster termination time
 - No need for screwdriver and torque wrench
 - Spring Termination eliminates strand relaxation
 - Funnel shaped wire entry for ease of termination.
 - Superior cord grip design protects terminations from excess strain

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Black Nylon	350"-1.150" (9-29) 7	783585719825	HBL2411STBK

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

Housing / Cord Clamp	Nylon
Terminal Retainer	Nylon
Plunger	Nylon
Blades	Copper Alloy
Terminal Spring Clamp	Spring Steel
Assembly Screws	Zinc Plated Tri-drive
Weight (lbs)	0.25

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions



Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 3,000V minimum
Mechanical	
Terminal Accommodation	#14 AWG - #8 AWG stranded copper wire only
Terminal Identification	Terminals identified in accordance with UL 498
Environmental	
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C, Minimum -40°C (w/o impact)

