

Twist-Lock® Edge Devices

20A, 125/250V AC; 3 Pole, 4 Wire Grounding

## Screwless Terminated InsulGrip® Connector

# HUBBELL

### Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Superior cord grip design protects terminations from excess strain

### Ordering Information

| Description | Cord Diameter      | UPC          | Catalog Number |
|-------------|--------------------|--------------|----------------|
| Black Nylon | .360"-.930" (9-24) | 783585730585 | HBL2413STBK    |

### Listings

Listed to UL 498  
Fed.Spec. W-C-596  
Certified to CSA C22.2 No.42

### Specifications

|                       |                       |
|-----------------------|-----------------------|
| Housing / Cord Clamp  | Nylon                 |
| Terminal Retainer     | Nylon                 |
| Plunger               | Nylon                 |
| Contacts              | Brass                 |
| Terminal Spring Clamp | Spring Steel          |
| Assembly Screws       | Zinc Plated Tri-drive |
| Weight (lbs)          | 0.4                   |

### Performance

|                         |                                                          |
|-------------------------|----------------------------------------------------------|
| <b>Electrical</b>       |                                                          |
| Current Interrupting    | Certified for current interrupting at full rated current |
| Dielectric Voltage      | Withstands 3,000V minimum                                |
| <b>Mechanical</b>       |                                                          |
| Terminal Accommodation  | #14 AWG - #8 AWG stranded copper wire only               |
| Terminal Identification | Terminals identified in accordance with UL 498           |
| <b>Environmental</b>    |                                                          |
| Flammability            | HB or better per UL94/CSA 22.2 No.0.17                   |
| Moisture Resistance     | IP20 Suitability                                         |
| Operating Temperatures  | Maximum Continuous 75°C, Minimum -40°C (w/o impact)      |



### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

