

Twist-Lock® Edge Devices

20A 3-Phase WYE 120/208VAC, 4-Pole 5-Wire

Screwless Terminated InsulGrip® Plug



- Features
- Faster termination time
  - No need for screwdriver and torque wrench
  - Spring Termination eliminates strand relaxation
  - Funnel shaped wire entry for ease of termination.
  - Superior cord grip design protects terminations from excess strain

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Black Nylon	350"-1.150" (9-29) 7	783585719832	HBL2511STBK

Listings

Listed to UL 498  
Fed.Spec. W-C-596  
Certified to CSA C22.2 No.42

Specifications

Housing / Cord Clamp	Nylon
Terminal Retainer	Nylon
Plunger	Nylon
Blades	Copper Alloy
Terminal Spring Clamp	Spring Steel
Assembly Screws	Zinc Plated Tri-drive
Weight (lbs)	0.3

Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions



Performance

<b>Electrical</b>	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 3,000V minimum
<b>Mechanical</b>	
Terminal Accommodation	#14 AWG - #8 AWG stranded copper wire only
Terminal Identification	Terminals identified in accordance with UL 498
<b>Environmental</b>	
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C, Minimum -40°C (w/o impact)

