Twist-Lock® Devices 20A, 3 Phase Y 120/208V AC, 4 Pole, 5 Wire Grounding

Safety-Shroud® Plug

Features

- Ribbed nylon housing provides a secure grip and impact and chemical resistance.
- Superior cord grip design protects terminations from excess strain.
- Integral dust shield protects wiring chamber from dust or contaminants.

Ordering Information

Description Black and white nylon body, white PBT shroud.

Cord Diameter **UPC** .350"-1.150" (9-29) 783585235028

Catalog Number

HBL2511S

Listings

Listed to UL 498 Fed.Spec. W-C-596

Certified to CSA C22.2 No.42

Specifications

White PBT Safety-Shroud® Nylon Housing / Cord Clamp

Terminal Retainer Clear polycarbonate

Blades **Brass**

Terminal Screws #10-32 Brass (Phillips / Slotted / Robertson)

Cold rolled steel - nickel plated Terminal Clamp

Assembly Screws Steel - nickel plated

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Withstands 2,000V minimum Dielectric Voltage

Mechanical

Terminal Accommodation #16 AWG - #8 AWG stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

V0 per UL94 or CSA 22.2 No.0.17 Flammability


Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C Minimum -40°C (w/o impact)

HUBBELL









Accessories

HBL2513 Connector HBL2510AR Receptacle - Angle Housing Receptacle - Surface Mount HBL2510SR Receptacle - Semi Flush HBL2510SR2

Resources

Customer Use Drawing eCatalog

