

Twist-Lock® Edge Devices

20A, 3 Phase Y 120/208V AC, 4 Pole, 5 Wire Grounding

Screwless Terminated InsulGrip® Flanged Receptacle



Features

- Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- Backwired termination for ease of installation

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Black Nylon casing, back wired	.360"-.930" (9-24)	783585749082	HBL2516STBK

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

Housing	Nylon
Terminal Retainer	Nylon
Plunger	Nylon
Contacts	Brass
Terminal Spring Clamp	Spring Steel
Assembly Screws	Zinc Plated Tri-drive
Weight (lbs)	0.4

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions



Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 3,000V minimum
Mechanical	
Terminal Accommodation	#14 AWG - #10 AWG solid or #14 AWG - #8 AWG stranded copper wire
Terminal Identification	Terminals identified in accordance with UL 501
Environmental	
Flammability	HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C, Minimum -40°C (w/o impact)

