

Twist-Lock® Devices 15A, 125V, 2 Pole, 3 Wire Grounding Elastogrip® Connector

HUBBELL

Features

- Integral weatherproofing shroud seals connection between plug and connector
- Nylon compression nut keeps water and dust from getting into the body around the cord

Ordering Information

Description	Cord Diameter	UPC	Catalog Number
Elastogrip Connector, yellow elastomer, dust tight	.300"- .655" (7.6-16.6)	783585235905	HBL2547

Listings

Listed to UL 498
Fed.Spec. W-C-596
Certified to CSA C22.2 No.42

Specifications

Terminal Retainer	Clear polycarbonate
Cord Clamp	Nylon
Contacts	Brass
Terminal Screws	Brass
Cord Clamp Screws	Steel, zinc plated
Assembly Screws	Steel, zinc plated

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current
Dielectric Voltage Withstand 2,000V minimum

Mechanical

Terminal Accommodation #18 AWG- #10 AWG stranded copper wire only.
Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL94/CSA 22.2 No.0.17
Moisture Resistance IP20 Suitability
Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)



Accessories

Plug	HBL2447
------	---------

Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

