Twist-Lock Devices 30A, 125V AC, 2 Pole, 3 Wire Grounding Screwless Terminated InsulGrip Connector

Features

- Faster termination time
- · No need for screwdriver and torque wrench
- · Spring Termination eliminates strand relaxation
- · Funnel shaped wire entry for ease of termination.
- · Superior cord grip design protects terminations from excess strain

Ordering Information

Description Black and white nylon.

cord Diameter a nylon. .360"-.930" (9-24)

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing / Cord Clamp Terminal Retainer Plunger Contacts Terminal Spring Clamp Assemby Screws Weight (lbs) Nylon Nylon Brass Spring Steel Zinc Plated Tri-drive 0.35

UPC

78358571928

Catalog Number

HBL2613ST

Online Resources

Customer Sales Drawings eCatalog

Performance

Electrical Current Interrupting Dielectric Voltage

Mechanical Terminal Accommodation

Terminal Identification

Environmental Flammability Moisture Resistance Operating Temperatures Certified for current interrupting at full rated current Withstands 3,000V minimum

#14 AWG - #8 AWG stranded copper wire only

Terminals identified in accordance with UL 498

HB or better per UL94/CSA 22.2 No.0.17 IP20 Suitability Maximum Continuous 75°C, Minimum -40°C (w/o impact)



Wiring Device-Kellems



HUBBELL