

Locking Devices

NEMA Twist-Lock

30A, 250V 2-Pole 3-Wire AC Insulgrip® Plug

HUBBELL

Ordering Information

Description	NEMA Rating	UPC	Catalog Number
Cord clamps with removable inserts	NEMA L6-30P	783585131153	HBL2621EBK

Specifications

Current/Amperage	30 A
Phase	Single Phase
Wire Size	#16 AWG to #8 AWG

Performance

Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical

Flammability	HB or better per UL94/CSA 22.2 No.0.17
Terminal Accommodation	#16 AWG - #8 AWG stranded copper wire only
Terminal Identification	Terminals identified in accordance with UL 498

Environmental

Moisture Resistance	IP20 Suitability
Operating Temperatures	Maximum Continuous 75°C; Minimum -40°C (w/o impact)



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

