Twist-Lock® Devices 30A, 250V AC, 2 Pole, 3 Wire Grounding Watertight Safety-Shroud® Plug



- Impact resistant shroud protects blades against bending and breaking.
- Reduces exposure to arcing when connecting or disconnecting under load.
- Superior cord grip design protects terminations from excess strain.

Catalog Number

HBL2621SW

Ordering Information

Description Cord Diameter UPC Black PBT housing, .325"- .930"(9-24) 783585231686 white PBT clamps.

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42 UL Listed, CSA Certified to Type 4, 4X and Type 12

Specifications


Housing / Cord Clamp	PBT
Terminal Retainer	Clear polycarbonate
Blades	Brass
Terminal Screws	#10-32 Brass (Phillips / Slotted / Robertson)
Terminal Clamp	Cold rolled steel – nickel plated
Assembly Screws	Stainless Steel
Watertight Gland	Neoprene
Closure Plug	Santoprene

Performance

Electrical Current Interrupting Dielectric Voltage	Certified for current interrupting at full rated current Withstands 2,000V minimum
Mechanical Terminal Accommodation	#16 AWG - #8 AWG stranded copper wire only.
Terminal Identification	Terminals identified in accordance with UL 498
Environmental Flammability Moisture Resistance Operating Temperatures	V0 per UL94 or CSA 22.2 No.0.17 Type 4, 4X, 12, IP66 suitability Maximum Continuous 75°C; Minimum -40°C (w/o impact)



HUBBELL



Accessories

Watertight Safety Shroud Connector	HBL2623SW
Watertight Safety Shroud Receptacle	HBL2620SW

Resources

Customer Use Drawing	
eCatalog	

