Twist-Lock® Devices 30A, 250V AC, 2 Pole, 3 Wire Grounding Valise® Plug

HUBBELL

Features

- Powerful cord grip prevents conductor slippage and strain on wiring terminals
- Totally insulated impact and crush resistant nylon body
- Unique patented clamp type terminals provide a superior electrical connection by bundling the conductor strands when clamps are tightened

Ordering Information

Description Black nylon.	Cord Diameter .590"930" (15.0-23.6)	UPC 783585043166	Catalog Number HBL2621VBK
	(15.0-23.6)		



Listings

Listed to UL 498 Fed.Spec. W-C-596

Certified to CSA C22.2 No.42


Specifications

Housing Black nylon Blades **Brass**

Terminal Screws #8 - 32 Steel (Philips / Slotted / Robertson)

Terminal Clamps Steel - Nickel plated

#8 - 32 Steel - Zinc plated (Philips / Slotted / Robertson) Clamp Screws



Performance

Electrical

Certified for full rated current **Current Interrupting** Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #14 AWG - #8 AWG stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

HB or better per UL 94 or CSA 22.2 No. 0.6 Flammability Moisture Resistance

IP20 Suitability

Operating Temperature Maximum continuous 75°C, minimum -40°C (w/o impact)

Accessories

Connector	HBL2623VBK
Single Receptacle	HBL2620
Flanged Receptacle	HBL2626
Weatherproof Boot	HBL60CM31V

Resources

Customer Use Drawing eCatalog

