Twist-Lock® Devices 30A, 250V AC, 2 Pole, 3 Wire Grounding Valise® Plug

HUBBELL

Features

- Powerful cord grip prevents conductor slippage and strain on wiring terminals
- Totally insulated impact and crush resistant nylon body
- Unique patented clamp type terminals provide a superior electrical connection by bundling the conductor strands when clamps are tightened

Ordering Information

Description Yellow nylon.	Cord Diameter .590"930" (15.0-23.6)	UPC 783585236025	Catalog Number HBL2621VY



Listings

Listed to UL 498 Fed.Spec. W-C-596

Certified to CSA C22.2 No.42


Specifications

Housing Yellow nylon Blades Brass

Terminal Screws #8 - 32 Steel (Philips / Slotted / Robertson)

Terminal Clamps Steel - Nickel plated

Clamp Screws #8 - 32 Steel - Zinc plated (Philips / Slotted / Robertson)



Performance

Electrical

Current Interrupting Certified for full rated current Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #14 AWG - #8 AWG stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL 94 or CSA 22.2 No. 0.6

Moisture Resistance IP20 Suitability

Operating Temperature Maximum continuous 75°C, minimum -40°C (w/o impact)

Accessories

Connector	HBL2623VY
Single Receptacle	HBL2620
Flanged Receptacle	HBL2626
Weatherproof Boot	HBL60CM31V

Resources

Customer Use Drawing eCatalog

