

## Locking Devices

### NEMA Twist-Lock

# 30A, 250V AC 2-Pole 3-Wire Insulgrip® Connector

# HUBBELL

## Ordering Information

| Description                        | NEMA Rating | UPC          | Catalog Number |
|------------------------------------|-------------|--------------|----------------|
| Cord clamps with removable inserts | NEMA L6-30R | 783585131160 | HBL2623EBK     |

## Specifications

|                  |      |
|------------------|------|
| Current/Amperage | 30 A |
|------------------|------|

## Performance

### Electrical

|                      |  |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage   | Withstands 2,000V minimum                                |

### Mechanical

|                         |  |
|-------------------------|--|
| Flammability            | HB or better per UL94/CSA 22.2 No.0.17         |
| Terminal Accommodation  | #16 AWG - #8 AWG stranded copper wire only     |
| Terminal Identification | Terminals identified in accordance with UL 498 |

### Environmental

|                        |   |
|------------------------|---|
| Moisture Resistance    | IP20 Suitability                                    |
| Operating Temperatures | Maximum Continuous 75°C; Minimum -40°C (w/o impact) |



## Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

