Twist-Lock Devices 30A, 250V, 2 Pole, 3 Wire Grounding Screwless Terminated InsulGrip Connector

HUBBELL

Features

- · Faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Funnel shaped wire entry for ease of termination.
- · Superior cord grip design protects terminations from excess strain

Ordering Information

UPC Description **Cord Diameter Catalog Number** .360"-.930" (9-24) HBL2623ST Black and white nylon. 78358571925

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing / Cord Clamp Nylon Terminal Retainer Nylon Nylon Plunger Contacts **Brass Terminal Spring Clamp** Spring Steel Assemby Screws Zinc Plated Tri-drive 0.35

Weight (lbs)



Online Resources

Customer Sales Drawings eCatalog

Performance

Electrical

Certified for current interrupting at full rated **Current Interrupting**

current

Dielectric Voltage Withstands 3,000V minimum

Mechanical

Terminal Accommodation #14 AWG - #8 AWG stranded copper wire only

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability HB or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C, Minimum -40°C

(w/o impact)

