Twist-Lock® Devices 30A, 277V AC, 2 Pole, 3 Wire Grounding Insulgrip® Flanged Receptacle

HUBBELL

Features

- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included



Ordering Information

Description Device Color Nylon casing, back wired White	UPC 783585038995	Catalog Number HBL2636
---	---------------------	---------------------------

Listings

Listed to UL 498
Fed.Spec. W-C-596

Certified to CSA C22.2 No.42

Specifications

Housing Nylon


Terminal Retainer Clear polycarbonate

Contacts Brass

Terminal Screws #10-32 Brass (Phillips / Slotted / Robertson)

Terminal Clamp Cold rolled steel – nickel plated

Assembly Screws Steel - nickel plated Mounting Screw Nickel plated brass



Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

Flammability V2 or better per UL94/CSA 22.2 No.0.17

Moisture Resistance IP20 Suitability

Operating Temperatures Maximum Continuous 75°C; Minimum -40°C (w/o impact)

Accessories

Plug	HBL2631
Weatherproof Lift Cover	WP2

[3.3]

Resources

Customer Use Drawing eCatalog

