# Hubbellock® Devices 60A, 600V AC, 3 Pole, 4 Wire Grounding Hubbellock® Connector

# HUBBELL

## **Features**

- · Spring loaded safety shutter contains arcing when mating or un-mating devices under load
- Spring loaded safety shutter automatically ejects the plug eliminating contact teasing
- Box terminals in conjunction with stainless steel screws provide maximum termination strength and dependability
- Insulated, color coded metallic housing enhances safety and abuse resistance

# **Ordering Information**

Description Black phenolic interior with yellow thermoplastic sleeve

**Cord Diameter UPC** .920"-1.450"(23.36 783585017310 -36.83)

Catalog Number HBL26418

over steel housing

Listings

Listed to UL 498 Certified to CSA C22.2 No. 42

# **Specifications**

**Device Color** Yellow

Steel Housing / Yellow Polycarbonate Cover Housing

Steel Cord Clamp Connector Interior Phenolic Contacts / Springs Copper alloy Terminal Copper

**Terminal Screws** Stainless steel

### **Performance**

**Electrical** 

**Current Interrupting** Certified for current interrupting at full rated current

Dielectric Voltage 2,000V minimum Withstand

Mechanical

Terminal Accommodation #8 AWG - #4 AWG stranded copper wire only.


Terminal Identification Terminals identified in accordance with UL 498

**Environmental** 

Flammability **UL 94 VO** Moisture Resistance IP30 Suitability

Maximum Continuous 75°C; Minimum -40°C (w/o impact) **Operating Temperatures** 





#### **Accessories**

Flanged Inlet	HBL26422
Plug	HBL26419

## Resources

Customer Use Drawing eCatalog

