# **Watertight Devices** 20A, 125V, 2 Pole, 3 Wire Twist-Lock ® Plug

# HUBBELL

#### **Features**

- Power indicating LED also confirms wiring condition of the device
- Smooth body design minimizes collection points simplifying the wash down process
- Strain relief nut always seals on the body, minimizing debris collection

### **Ordering Information**

Description Thermoplastic elastomer clear plug

Cord Diameter UPC Number 0.375"-0.875" (9.5-22.2)

**Catalog Number** HBL26W47WC 78358558061

### Listings

Listed to UL498 Certified to CSA C22.2 No. 42 Meets NEMA WD-1, WD-6 and ANSI standards UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P

# **Specifications**

Body Thermoplastic Elastomer

Blade Holder White Nylon Clear polycarbonate Terminal Retainer Nickel plated brass Blades White Nylon Core **Bushing & Cone Seal** Black Elastomer

Gotcha Ring Nylon Strain Relief Nut PBT

Nickel plated brass **Terminal Screws** 

#### **Performance**

**Electrical** 

**Current Interrupting** Rated for current interruption per UL498

Dielectric Voltage 2500V AC Max Working Voltage As marked

Temperature Rise 30°C max per UL498 at rated current

Mechanical

Cord Accomodation 0.375"-0.625" (9.5-15.9)

**Environmental** 

UL Listed 4, 4X, 12, 6, 6P Moisture Resistance

Operating Temperature -40°C (without impact) to +60°C continuous **UV** resistance All exposed materials are UV stabilized



## **Complementary Products**

Watertight Connector HBL27W47WC Watertight Receptacle with Lift Cover HBL67W47

#### Online Resources

eCatalog Installation Instructions

