Twist-Lock® Devices 30A, 125/250V AC, 3 Pole, 4 Wire Grounding Insulgrip® Flanged Inlet

HUBBELL

Features

- Backwired terminations for ease of installation
- #10-32 Multiple drive terminal screws (Slotted, Phillips, Robertson)
- Mounting screws included

Ordering Information

Description Nylon casing, weather protective, die cast aluminum, back wired, self closing lift cover.

Device Color

UPC 783585039961

Catalog Number HBL2715M3

Listings

Listed to UL 498 Fed.Spec. W-C-596 Certified to CSA C22.2 No.42

Specifications

Housing / Flange Terminal Retainer Nylon Clear polycarbonate

Blades **Brass**

Terminal Screws #10-32 Brass (Phillips / Slotted / Robertson)

Cold rolled steel - nickel plated Terminal Clamp

Steel - nickel plated Assembly Screws

Cover Assembly Cast Aluminum with powder coat paint

Mounting Screw Stainless Steel

Performance

Electrical

Current Interrupting Dielectric Voltage

Certified for current interrupting at full rated current

Withstands 2,000V minimum

Mechanical

Terminal Accommodation #16 AWG - #8 AWG solid or stranded copper wire only.

Terminal Identification Terminals identified in accordance with UL 498

Environmental

HB or better per UL94/CSA 22.2 No.0.17 Flammability

Moisture Resistance IP20 Suitability

Maximum Continuous 75°C. Minimum -40°C (w/o impact) **Operating Temperatures**



Accessories

Connector HBL2713

Resources

eCatalog

